

**Mobile workbench 179NW, Type: 179NW-7****Order data**

Order number	918279 179NW-7
GTIN	4000896219629
Item class	93H

**Description****Version:**

Mobile workbench with 7 drawers and cupboard section with an adjustable shelf. Central locking with cylinder lock and anti-tilt device on both sides. Cabinet with edge protection corners throughout. Drawer load capacity 25 kg, one heavy-duty drawer rated at 40 kg load capacity. Worktop made of Birch marine ply, suitable for flexible mounting of vice, exchangeable. Overall load capacity 750 kg. 2 castors with parking brake, and 2 fixed wheels.

**Fitted with:**

Number x drawer front height mm: 6 x 81 / 1 x 166

**Colour:**

Blue

Drawer runner extension: Anti-tilt lock

Height: 964 mm

Width: 1150 mm

Depth: 600 mm

Worktop thickness: 30 mm

Drawer usable width: 522 mm

Drawer usable depth: 398 mm

**Technical description**

Drawer usable width	522 mm
Weight	120 kg
Height	964 mm
Drawer usable depth	398 mm
Series	Assistent
Worktop thickness	30 mm
Depth	600 mm
Width	1150 mm
Type	179NW-7
Drawer/pull-out shelf load capacity	25 kg
Drawer runner extension (partial/full extension)	100 %
Drawer runner extension	Anti-tilt lock
Type of product	Mobile workbench

## Accessories

Drawer · high	179NW-051
Edge protection · bottom	179N-093A
Cylinder lock	179NW-08
Telescopic rails · pair	179N-07/2
Drawer · flat	179N-050
Edge protection · bottom	179N-093B
Worktop · wood	179NW-05
Edge protection · top	179NW-094
Shelf	179NW-23
Locking bar	179NW-04
Upper edge protection	179NW-094B
Door · lockable	179NW-21
Magnetic catch	179NW-012

Edge protection · bottom	179N-093
Fixed castor	179NW-09A
Drawer locking hook	179N-019
Lock set	179TXXL-08/2
Telescopic rails · pair	179NXL-07/2
Swivel castor · with brake	179NW-011A
Edge protection · top	179NW-094A
Handle profile for drawers	179N-057