

Garant GRIDLINE

Top-mounted cabinet with drawer, Plain sheet metal sliding doors, 26×14G, Height: 750mm



Order data

Order number	940195 750
GTIN	4062406069971
Item class	9GI

Description

Version:

Equipped cabinet in 60×20G, with drawers 26×14G. Mountings for shelves at 25 mm intervals. Sliding doors reinforced on the inside and can be locked by 2-component Haptoprene® handle using a cylinder lock. Locks the sliding doors in the end positions (open/closed). **Levelling base** for base cabinets, with 8 individually adjustable feet to compensate for unevenness in the floor. In the base cabinet the handle is mounted in the upper part of the door; in the top-mounted cabinet it is in the lower part of the door.

drawers with front height 125 mm.

Supplied with:

Cabinet with shelves and drawers.

Colour:

Body and drawer cabinet body RAL 7035 light grey, doors and drawer fronts RAL 7016 anthracite **powder-coated**.

Note:

For storage shelves and accessories for GridLine cabinets see No. 940501 – 940710 and Group 95. According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Height	750 mm
ComfortClose	no

Number of shelves	2
Width	1500 mm
Width in G	60
Depth in G	20
Drawer/pull-out shelf load capacity	75 kg
Handle positioning	bottom
Drawer usable area in G	26×14
Drawer usable depth in G	14
Weight	90 kg
Drawer usable depth	350 mm
Number of drawers	2
Shelf load capacity / maximum distributed shelf load (on metal)	100 kg
Depth	500 mm
Drawer runner extension (partial/full extension)	100 %
Electronic locking system can be retrofitted	yes
Drawer usable width in G	26
Usable height	613 mm
Drawer usable width	650 mm
Material thickness	0.9 mm
Cabinet housing internal load capacity	1000 kg
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×14G
Type of cabinet	Add-on cabinet
Type of product	Cabinet with shelves

Accessories

Extended lighting set for GridLine cabinets with Sliding doors, width 60G for cabinet height 750/800 mm

940514 750/800

Comfort Close drawer closure damping system Load capacity of the drawer 75 kg

950180 75