

Garant**INFO Point for individual configuration, Type: M****Order data**

Order number	948010 M
GTIN	4062406072452
Item class	9GS

Description**Version:**

GARANT INFO Point is a modern computer workstation for the display and processing of digital information, for recording data and as a response station with a connected barcode scanner (not supplied).

The INFO Point has a sturdy sheet metal housing. A swing-open tray is mounted on the front at an ergonomic height to accept a keyboard and computer mouse. A PC or Linux client can be mounted within the body underneath the tray behind the lockable door. The tray and the door can be locked with DOM cylinder locks. A perforated panel with holes of $\square 9 \times 9$ mm on a 37 mm grid is provided at the back of the body for the necessary ventilation of the devices mounted within the body. Easyfix hooks and holders can also be mounted on the panel.

Without monitor, for individual configuration with a 24 inch monitor. Maximum possible screen size: Width 525 mm, height 315 mm, depth 90 mm. Mobility unit with 4 castors (\varnothing 100 mm), 2 with parking brake.

Fitted with:

Number of shelves in the computer housing: 1

Colour:

Body anthracite RAL 7016 **powder-coated**.

Technical description

Weight	65 kg
Computer housing usable height	740 mm
Footprint depth	550 mm
Computer housing usable width	540 mm
Counter depth	300 mm
Footprint width	616 mm
Height	1570 mm
Computer housing usable depth	190 mm
Counter width	600 mm
Counter working height	1060 mm
Power supply	Mains operated
Tray closed, depth	150 mm
Material thickness	0.9 mm
Hoffmann perforated panel grid interval	9×9 mm
Cylinder lock	modular lock barrel
Type of product	INFO Point