

Garant**Storage cabinet with viewing window swing doors, Number of transparent boxes: 97****Order data**

Order number	944113 97
GTIN	4062406073473
Item class	9GI

Description**Version:**

Equipped storage cabinet in 30×11G.

Transparent boxes of ABS plastic for dust-free storage. Tilt the transparent box to remove stored goods. Bins can be removed and stacked for assembly purposes.

Doors reinforced on the inside and can be locked by 2-component Haptoprene® push handle using a **cylinder lock**.

Fitted with:

Number of transparent boxes (W×D×H): 36 pcs. 50×42×46 mm 36 pcs. 80×63×70 mm 25 pcs. 100×97×108 mm

Supplied with:

Cabinet with transparent boxes.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Weight	70.5 kg
Height	2000 mm
Width	750 mm
Depth	275 mm
Depth in G	11
Width in G	30
Material thickness	0.9 mm
Cabinet housing internal load capacity	500 kg
Door opening angle	250 degrees
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Storage cabinet

Accessories

Slide handle for GridLine Type GP11	914226 GP11
-------------------------------------	-------------