

Garant

Machine tap for synchronised spindles HSS-E-PM IC / Form C, TiAlN, MF: 10X1



Order data

| | |
|--------------|---------------|
| Order number | 137186 10X1 |
| GTIN | 4045197705440 |
| Item class | 11H |

Description

Version:

Sturdy version with right-hand helix and shank to DIN 1835-B. Special geometry for **general-purpose use** on machines with **synchronised spindle drive**. The tap is controlled by the synchronising spindle of the machine. Special **TiAlN-S coating** for optimum tool life. For use with **emulsion** (fat content minimum 8%).

With **internal coolant supply** for maximum tool life.

Note:

For use on synchronised spindles, the **GARANT** quick-change tapping chuck **No. 338100 – 338121 with minimum length adjustment (MLA)** ensures very high process reliability.

Thread type: MF

Tool material: HSS E PM

Standard: Manufacturer's standard

Tolerance class: ISO 2X 6HX

Thread pitch: 1 mm

Overall length L: 90 mm

Shank $\varnothing D_s$: 10 mm

Shank square \square : 8 mm

Tapping hole \varnothing : 9 mm

Technical description

| | |
|----------------------------|-------|
| Thread pitch | 1 mm |
| Number of cutting edges Z | 3 |
| Number of clamping slots | 3 |
| Tapping hole \varnothing | 9 mm |
| Thread \varnothing | 10 mm |

| | |
|----------------------------------|---------------------------------------|
| Shank $\varnothing D_s$ | 10 mm |
| Overall length L | 90 mm |
| Shank square \square | 8 mm |
| Tolerance class | ISO 2X 6HX |
| Tool material | HSS E PM |
| Standard | Manufacturer's standard |
| Thread depth | 30 mm |
| Thread type | MF |
| Thread size | M10x1 |
| Coating | TiAlN |
| Flank angle | 60 ° |
| Thread standard | DIN 13 |
| Taper lead form | C |
| Helix angle | 40 ° |
| Shank | DIN 1835 B with h6 |
| Through-coolant | yes |
| Application for type of drilling | up to 3xD for blind holes |
| Cutting direction | right-hand |
| Shank tolerance | h6 |
| Type of threading tool | Machine tap for synchronous machining |
| Colour ring | green |
| Type of product | Tap |

User data

| | Suitability | V_c | ISO code |
|----------------------------|---|----------|----------|
| Alu plastics | suitable only under restricted conditions | 32 m/min | N |
| Aluminium (short chipping) | suitable | 32 m/min | N |

| | | | |
|--------------------------------|--|----------|---|
| Steel < 500 N/mm ² | suitable | 33 m/min | P |
| Steel < 750 N/mm ² | suitable | 32 m/min | P |
| Steel < 900 N/mm ² | suitable | 20 m/min | P |
| Steel < 1100 N/mm ² | suitable | 12 m/min | P |
| Steel < 1400 N/mm ² | suitable | 7 m/min | P |
| INOX < 900 N/mm ² | suitable | 11 m/min | M |
| INOX > 900 N/mm ² | suitable | 9 m/min | M |
| CuZn | suitable only under restricted conditions | 30 m/min | N |
| Uni | suitable | | |
| Oil | suitable | | |
| wet maximum | suitable | | |
| wet minimum | suitable | | |