

Garant GRIDLINE

Battery charging cabinet with Viewing window swing doors, Height: 2000/DEmm



Order data

Order number	944503 2000/DE
GTIN	4062406073589
Item class	9GI

Description

Version:

Equipped battery charging cabinet in 40×20G, with **earth leak trip fuse box** and **fan**. Fan with air filter in overpressure operation (50 m³ / h). Air escapes through horizontal ventilation slots in the doors. Battery charging shelves each with two 6-way 230 V socket strips with ON/OFF switch.

Supplied with:

Cabinet supplied with 2 perforated battery charging shelves. Connection plug 16 A / 400 V 5-pin with 3 m cable and **measurement certificate**. 4 × 6-way socket strip. In addition, 2 storage shelves No. 940550 size 40 and 1 drawer No. 940642 size 125.

Colour:

Body RAL 7035 light grey, doors RAL 7016 anthracite **powder-coated**.

Note:

German socket version.

According to the TÜV GS certification, it is essential that all cabinets are secured against tipping over.

Technical description

Number of sockets	24
-------------------	----

Height	2000 mm
Weight	120 kg
Width	1000 mm
Depth	500 mm
Usable height	1845 mm
Width in G	40
Depth in G	20
Power supply	Mains operated
Nominal voltage	400 V
On/Off switch	yes
Plug type, input	F
Number of sockets type F	24
Socket type	F
Material thickness	0.9 mm
Door opening angle	250 degrees
Height adjustment interval	25 mm
Cylinder lock	modular barrel
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Type of product	Battery charging cabinet

Accessories

Slide handle for GridLine Type GP11	914226 GP11
Drawer for swing-door cabinets,Width 40G Drawer front height 125 mm	940642 125
Storage shelf for cabinet / compartment width in G 40	940550 40