

**Garant**
**GARANT Master Steel SPEED solid carbide drill, Weldon shank DIN 6535 HB, TiAlN, Ø DC h7: 14,06-Xmm**

**Order data**

Order number	122416 14,06-X
GTIN	4062406077105
Item class	11E

**Description**
**Version:**

Developed for use with **very high cutting speeds**. Outstandingly suitable for machines with **low installed power** and high speeds.

- **Clear reduction in cutting forces due to special cutter geometry.**
- **Coating for best wear resistance even at high process temperatures.**
- **Polished flutes for good chip clearance.**

A **slim chisel point** and the **special arrangement of the 4 guide chamfers** ensure **high positioning and alignment accuracy**. Optimised micro-geometry for increased working life and performance capability.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ . Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned. We reserve the right to over-deliver or under-deliver by  $\pm 10\%$  (minimum 1 piece).

**Technical description**

Shank $\varnothing D_s$	16 mm
Number of cutting edges Z	2
Tolerance nominal $\varnothing$	h7
Flute length $L_c$	65 mm
Standard	DIN 6537 K

Overall length L	115 mm
Feed f in steel < 1100 N/mm <sup>2</sup>	0.31 mm/rev.
Ø range	14.06 - 16.05 mm
Series	Master Steel
Coating	TiAlN
Tool material	solid carbide
Version	4xD
Point angle	135 degrees
Shank	DIN 6535 HB to h6
Through-coolant	no
Machining strategy	HPC
Semi-Standard	yes
Colour ring	green
Type of product	Jobber drill

## User data

	Suitability	V <sub>c</sub>	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	150 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	120 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable only under restricted conditions	60 m/min	P
GG	suitable	110 m/min	K
GGG	suitable	100 m/min	K
Uni	suitable		
wet maximum	suitable		

