



Solid carbide high performance drill, plain shank DIN 6535 HA, TiN, Ø DC h7 (mm or inch): 16,06-X



Order data

| | |
|--------------|----------------|
| Order number | 122340 16,06-X |
| GTIN | 4062406076238 |
| Item class | 12E |

Description

Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. **Straight major cutting edges** with slightly honed edges and special flute profile produce **short chips**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

NEW GENERATION AVAILABLE!

Recommended successor product is No. 122504.

Versions with HB and HE shank available at the same price as HA.

HB shank: use order **No. 122345**.

HE shank: use order **No. 122355**. Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned. We reserve the right to over-deliver or under-deliver by $\pm 10\%$ (minimum 1 piece).

Technical description

| | |
|--|--------------|
| Feed f in steel $< 900 \text{ N/mm}^2$ | 0.28 mm/rev. |
| Flute length L_c | 73 mm |
| Overall length L | 123 mm |
| Standard | DIN 6537 K |
| Shank $\varnothing D_s$ | 18 mm |

| | |
|---------------------------------|-------------------|
| Number of cutting edges Z | 2 |
| Tolerance nominal \varnothing | h7 |
| \varnothing range | 16.06 - 18.05 mm |
| Coating | TiN |
| Tool material | Solid carbide |
| Version | 4xD |
| Point angle | 140 degrees |
| Shank | DIN 6535 HA to h6 |
| Through-coolant | yes, with 25 bar |
| Semi-Standard | yes |
| Colour ring | green |
| Type of product | Jobber drill |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|-----------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | 240 m/min | N |
| Steel < 500 N/mm ² | suitable | 110 m/min | P |
| Steel < 750 N/mm ² | suitable | 90 m/min | P |
| Steel < 900 N/mm ² | suitable | 80 m/min | P |
| Steel < 1100 N/mm ² | suitable only under restricted conditions | 65 m/min | P |
| Steel < 1400 N/mm ² | suitable only under restricted conditions | 35 m/min | P |
| INOX < 900 N/mm ² | suitable | 35 m/min | M |
| INOX > 900 N/mm ² | suitable | 30 m/min | M |
| Ti > 850 N/mm ² | suitable | 30 m/min | S |
| Uni | suitable | | |
| wet maximum | suitable | | |
| wet minimum | suitable | | |

Air

suitable only under
restricted conditions