

Garant
Solid carbide HPC drill Weldon shank DIN 6535 HB, DLC, Ø DC h7: 3,76-Xmm


Order data

| | |
|--------------|---------------|
| Order number | 122307 3,76-X |
| GTIN | 4062406075835 |
| Item class | 11E |

Description

Version:

DLC coating sp^2 of the latest generation with **low coefficient of friction** results in **outstanding chip clearance**. For **high-performance milling** of aluminium materials. **High roundness** and **alignment accuracy of the deep hole**, thanks to **6 guide chamfers**.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$. Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned. We reserve the right to over-deliver or under-deliver by $\pm 10\%$ (minimum 1 piece).

Technical description

| | |
|------------------------------------|----------------|
| Feed f in aluminium short-chipping | 0.35 mm/rev. |
| Tolerance nominal Ø | h7 |
| Flute length L_c | 24 mm |
| Overall length L | 66 mm |
| Shank Ø D_s | 6 mm |
| Number of cutting edges Z | 2 |
| Standard | DIN 6537 K |
| Ø range | 3.76 - 4.75 mm |
| Coating | DLC |

| | |
|--------------------|-------------------|
| Tool material | solid carbide |
| Version | 4xD |
| Type | W |
| Point angle | 135 degrees |
| Shank | DIN 6535 HB to h6 |
| Through-coolant | Yes, with 25 bar |
| Machining strategy | HPC |
| Semi-Standard | yes |
| Colour ring | yellow |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|----------------------------|-------------|----------------|----------|
| Alu plastics | suitable | 360 m/min | N |
| Aluminium (short chipping) | suitable | 400 m/min | N |
| Alu > 10% Si | suitable | 350 m/min | N |
| PMMA acrylic | suitable | 150 m/min | N |
| PEEK | suitable | 120 m/min | N |
| PVDF GF20 | suitable | 90 m/min | N |
| PA 66 GF30 | suitable | 80 m/min | N |
| PEEK GF30 | suitable | 70 m/min | N |
| PTFE CF25 | suitable | 80 m/min | N |
| Cu | suitable | 160 m/min | N |
| CuZn | suitable | 200 m/min | N |
| GRP | suitable | 80 m/min | N |
| CRP | suitable | 80 m/min | N |
| wet maximum | suitable | | |
| wet minimum | suitable | | |

