

**Garant**
**Solid carbide HPC drill Weldon shank DIN 6535 HB, DLC, Ø DC p6: 8,06-Xmm**

**Order data**

Order number	122608 8,06-X
GTIN	4062406078256
Item class	11E

**Description**
**Version:**

Spiral fluted, with **6 guide chamfers** and internal cooling channels.

New generation of high performance pilot drills in the HPC range.

With **140° point angle** and special **p6 cutting edge tolerance** for optimum generation of a pilot hole. High alignment accuracy and **roundness of the pilot hole**.

**Note:**

Flute length  $L_c = L_2 + 1.5 \times D_c$ .

For deep-hole drilling deeper than  $16 \times D$  a pilot hole is recommended, and for deep-hole drilling from  $20 \times D$  to  $30 \times D$  it is essential. **The generation of a pilot hole always improves process reliability.** Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned. We reserve the right to over-deliver or under-deliver by  $\pm 10\%$  (minimum 1 piece).

**Technical description**

Tolerance nominal Ø	h7
Overall length L	103 mm
Feed f in aluminium short-chipping	0.36 mm/rev.
Flute length $L_c$	61 mm
Number of cutting edges Z	2
Standard	DIN 6537

Shank $\varnothing D_s$	10 mm
$\varnothing$ range	8.06 - 10.05 mm
Coating	DLC
Tool material	Solid carbide
Version	6xD
Type	W
Point angle	140 degrees
Shank	DIN 6535 HB to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	yellow
Type of product	Jobber drill

## User data

	Suitability	$V_c$	ISO code
Alu plastics	suitable	360 m/min	N
Aluminium (short chipping)	suitable	400 m/min	N
Alu > 10% Si	suitable	350 m/min	N
PMMA acrylic	suitable	150 m/min	N
PEEK	suitable	120 m/min	N
PVDF GF20	suitable	90 m/min	N
PA 66 GF30	suitable	80 m/min	N
PEEK GF30	suitable	70 m/min	N
PTFE CF25	suitable	80 m/min	N
Cu	suitable	160 m/min	N
CuZn	suitable	200 m/min	N
GRP	suitable	80 m/min	N

CRP	suitable	80 m/min	N
wet maximum	suitable		
wet minimum	suitable		