

Garant

Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC h7: 3,76-Xmm



Order data

| | |
|--------------|---------------|
| Order number | 123101 3,76-X |
| GTIN | 4062406079963 |
| Item class | 11E |

Description

Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**.

Particularly high alignment accuracy due to **4 guide chamfers** which stabilise the drill even at extreme depths!

Convex cutting edges with honed edges and special flute profile for **short chips**, even on long chipping materials.

Advantage:

High process reliability and surface quality of the hole.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Form **HB** and **HE** supplied at the same price as HA.

Form **HB**: order with **No. 123102**.

Form **HE**: order with **No. 123101 + 129100 HE**.

NEW GENERATION AVAILABLE!

Recommended successor products are No. 123025 and 123035. Delivery time: 12 working weeks

Minimum order quantity: 3 pcs

Items made to order for a specific customer:

Cancellation only up to a maximum of 3 working days after receipt of order acknowledgement.

Items cannot be returned. We reserve the right to over-deliver or under-deliver by $\pm 10\%$ (minimum 1 piece).

Technical description

| | |
|------------------------|-------------------------|
| Standard | Manufacturer's standard |
| Shank Ø D _s | 6 mm |

| | |
|---------------------------------|-------------------|
| Tolerance nominal \varnothing | h7 |
| Number of cutting edges Z | 2 |
| Flute length L_c | 43 mm |
| Overall length L | 81 mm |
| \varnothing range | 3.76 - 4.75 mm |
| Coating | TiAlN |
| Tool material | Solid carbide |
| Version | 8xD |
| Point angle | 135 degrees |
| Shank | DIN 6535 HA to h6 |
| Through-coolant | yes, with 25 bar |
| Machining strategy | HPC |
| Semi-Standard | yes |
| Colour ring | green |
| Type of product | Jobber drill |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|-----------|----------|
| Aluminium (short chipping) | suitable only under restricted conditions | 180 m/min | N |
| Alu > 10% Si | suitable only under restricted conditions | 140 m/min | N |
| Steel < 500 N/mm ² | suitable only under restricted conditions | 110 m/min | P |
| Steel < 750 N/mm ² | suitable | 90 m/min | P |
| Steel < 900 N/mm ² | suitable | 80 m/min | P |
| Steel < 1100 N/mm ² | suitable | 50 m/min | P |
| Steel < 1400 N/mm ² | suitable | 35 m/min | P |
| INOX < 900 N/mm ² | suitable only under restricted conditions | 40 m/min | M |

| | | | |
|------------------------------|---|----------|---|
| INOX > 900 N/mm ² | suitable only under restricted conditions | 35 m/min | M |
| GG(G) | suitable | 70 m/min | K |
| Uni | suitable | | |
| wet maximum | suitable | | |