


 KOMET**KOMET® indexable insert, K10, Designation: 26-660****Order data**

Order number	216740 26-660
GTIN	4047109036932
Item class	24T

Description**Version:**

With all-round chip breaker groove.

Suitable for :

Countersinking mill No. 216600 and 216620.

Corner radius: 0.5 mm

ISO code indexable insert: TOHX 140305 EN

Technical description

ISO code indexable insert	TOHX 140305 EN
Corner radius	0.5 mm
Number of changes/inserts	3
Grade	K10
Tool material	Carbide
Type of product	Indexable insert for milling

User data

	Suitability	V_c	ISO code
GG(G)	suitable	150 m/min	K
wet maximum	suitable		
dry	suitable		