

Garant**Indexable insert for milling AN.U 120608, for indexable milling cutters****Order data**

Order number	215113 UNI
GTIN	4045197703187
Item class	21A

Description**Version:**

Very sturdy double-sided 4-edge indexable insert.

The unique indexable insert geometry means the insert is not weakened by the securing hole.

Cutting dataa:

$a_{p\ max} = 12\ mm$.

$a_p = 10\ mm$ (recommendation).

Attention:

Not suitable for full-slot milling.

Note:

Side milling: Standard application values for $a_e = 0.3 \times D$ / $a_p = 10\ mm$.

Technical description

Type	UNI
Corner radius	0.8 mm
Type	HB925
Tolerance	K

ISO code indexable insert	AN.U 120608
Tool material	Carbide
Type of product	Indexable insert for milling