



## Ultradźwiękowe urządzenie do czyszczenia Elmasonic xtra ST, Typ: 50



### Dane zamówienia

Numer katalogowy	082002 50
GTIN	
Klasa artykułu	04S

### Opis

#### Wykonanie:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaner depending on the dirt and effectiveness required. The component to be cleaned must be completely surrounded by cleaning fluid.

Elmasonic xtra ST is the ultrasonic device for the most severe dirt and is particularly suitable for extremely demanding applications in the field of industrial cleaning.

- **2 selectable ultrasonic frequencies (25 kHz for the most stubborn dirt and 45 kHz for gentle cleaning).**
- **Integrated sweep function for even sound distribution in the cleaning bath.**
- **Selectable pulse function increases the ultrasonic peak power.**
- **Dynamic function (ultrasonic power can be increased temporarily by up to 20%).**
- **Sturdy tray made from welded stainless steel.**

pojemność: 48,7 l

długość urządzenia: 655 mm

szerokość urządzenia: 555 mm

długość kosza wsadowego: 255 mm

Szerokość kosza wsadowego: 230 mm

wysokość pojemnika do czyszczenia: 480 mm

## Opis techniczny

zasilanie energią	Zasilanie sieciowe
Moc szczytowa ultradźwięków	2400 W
długość urządzenia	655 mm
napięcie znamionowe	220 - 240 V
moc grzewcza	1400 W
szerokość urządzenia	555 mm
oznaczenie producenta	xtra ST 500H
długość kosza wsadowego	255 mm
masa	45 kg
wysokość pojemnika do czyszczenia	480 mm
Szerokość kosza wsadowego	230 mm
pojemność	48,7 l
zalecana objętość robocza	42 l