



## Dados do pedido

Número do pedido	919923 450
GTIN	4017976247021
Classe de artigo	96D

## Descrição

### Modelo:

Oil-tight welded skip, on bearings for tipping.

Skip edge folded over twice at the top.

Chassis with integral fork lift slots, standing area and tilt lock.

2 fixed wheels and 2 castors (with parking brake) with TPE tyres, hubs with grooved ball bearings.

TOTALSTOP - central braking system to EN 1757-3 fitted as standard to the castors.

### Norma:

**EN 1757-3**

## Descrição técnica

Material roda	TPE
Modelo da torneira de descarga	Torneira de descarga com crivo
Comprimento	1374 mm
Aberturas de acesso Medida C	603 mm
Aberturas de acesso Medida D	72 mm

Altura da borda de descarga com rodas	733 mm
Peso	83 kg
Cabo de tração	não
Aberturas de acesso Medida A	194 mm
Cor	cinzento antracite RAL 7016
com soldadura impermeável ao óleo	sim
Número de rodas	4
Medida comprimento da caixa	1214 mm
Capacidade de carga	750 kg
Volume do compartimento	450 l
Norma	EN 1757-3
Medida altura da caixa	708 mm
Altura	1072 mm
Distância entre as aberturas de acesso B	203 mm
Dimensões interiores de entrada, largura	194 mm
Mecanismo basculante	manual
Ø da roda	200 mm
Proteção contra viragem	sim
Dimensões interiores de entrada, altura	72 mm
Medida largura da caixa	669 mm
Largura	730 mm
com aberturas de acesso	sim
Tipo de produto	Contentor basculante