



Dados do pedido

Número do pedido	296325 16
GTIN	4045197518521
Classe de artigo	22E

Descrição

Modelo:

Carbide – steel shanks with 700 - 800 N/mm² strength and flat chamfered mounting surface. Fitted with diamond ground carbide inserts. Angles on the inserts are precision ground. All turning tools are supplied with sharp cutting edges. Sharpening the cutting edge with a boron carbide hand lapper will increase the tool edge life. The extent of the wear area is dependent on the cutting conditions. For roughing and interrupted machining it is imperative that the cutting edges are sharpened.

Fitted with diamond ground carbide inserts.

Descrição técnica

para furos de Ø a partir de	27 mm
Quadrado da haste	16 mm
Comprimento total	210 mm
Óleo de corte	P20/K25
Tipo de produto	Ferramenta de toronar