

● INNOVATEST®



Dados do pedido

Número do pedido	495073 605RS
GTIN	
Classe de artigo	49G

Descrição

Modelo:

Rockwell hardness testing machine with very high precision. Stiff machine frame, suitable even for rough workshop conditions.

Large 6.5" industrial colour touch screen. Test load release by touch screen with electronic monitoring of the dwell time. Test load application within the closed control loop (**load cell, closed loop system**). Integrated display and control electronics with touch-panel operation.

Norma:

DIN EN ISO 6508 und ASTM E-18, ISO 2039/1.

Descrição técnica

Força de ensaio da pré-carga	3; 10 kg
Peso	82 kg
largura máxima da amostra	250 mm
Designação do fabricante	NEXUS 610RS
Operação	motorizado
Leitura	1 HR

Método de teste	Rockwell / Super-Rockwell
Interface	USB-2
Alimentação elétrica	220 – 240 V / 50 Hz
Altura	855 mm
Largura	250 mm
altura máxima da amostra	165 mm
Indicação	ecrã tátil de 6,5 polegadas
Força de ensaio da carga principal	15; 30; 45; 60; 100; 150 kg
Escalas Rockwell	A, B, C, D, E, F, G, H, K, L, M, P, R, S, N, T, V, W, X, Y
Comprimento	505 mm
Alimentação de energia	A energia elétrica
Calibração	Preço sob consulta
Tipo de produto	Durómetro