



## Dados do pedido

Número do pedido	919922 250
GTIN	4017976847016
Classe de artigo	96D

## Descrição

### Modelo:

Oil-tight welded skip, on bearings for tipping.

Skip edge folded over twice at the top.

Chassis with integral fork lift slots, standing area and protection against overturning.

2 fixed wheels and 2 castors (with parking brake) with TPE tyres, hubs with grooved ball bearings.

TOTALSTOP - central braking system to EN 1757-3 fitted as standard to the castors.

### Norma:

**EN 1757-3**

## Descrição técnica

Número de rodas orientáveis com travão imobilizador	2
Largura	713 mm
Altura	780 mm
Número de rodas	4
Aberturas de acesso Medida D	72 mm
Cabo de tração	não
Volume do compartimento	250 l
Medida altura da caixa	413 mm

com aberturas de acesso	sim
com soldadura impermeável ao óleo	sim
Mecanismo basculante	manual
Modelo da torneira de descarga	Torneira de descarga com crivo
Proteção contra viragem	sim
Peso	70 kg
Comprimento	1359 mm
Distância entre as aberturas de acesso B	203 mm
Material roda	TPE
Aberturas de acesso Medida A	194 mm
Ø da roda	200 mm
Aberturas de acesso Medida C	603 mm
Dimensões interiores de entrada, altura	72 mm
Número de rodas fixas sem travão imobilizador	2
Capacidade de carga	750 kg
Altura da borda de descarga com rodas	780 mm
Medida largura da caixa	652 mm
Dimensões interiores de entrada, largura	194 mm
Medida comprimento da caixa	1200 mm
Cor	cinzento-claro RAL 7035
Norma	EN 1757-3
Tipo de produto	Contentor basculante