

## Indukčný zahrievací prístroj, Velkosť: 45



### ÚDAJE O OBJEDNÁVKE

Číslo objednávky	883962 45
GTIN	2050002076488
Trieda položky	86H

### Popis

**Prevedenie:**

The compact simatherm® induction heating device for rolling bearings and other ring-shaped metal parts for bore diameters from 20 to 310 mm. Roller bearings and other ring-shaped metal parts can be brought up to the 110 °C specified by the manufacturer under automatic control of time and temperature. Particularly compact design – only 17 kg in weight including 3 yokes. Remote control possible via Bluetooth mobile devices (only with free app “World of Maintenance”)

**Rozsah balenia:**

Ohrievací prístroj, 3 jarmá, teplotná sonda a rukavice s tepelnou ochranou.

### Technický opis

Šírka	268 mm
Teplota Rozsah regulácie	20 - 180 °C
Vonkajší Ø obrobku do	310 mm
maximálna hmotnosť obrobku	45 kg
Napätie	230 V
Výkon	2,1 kW

Dĺžka	320 mm
Vnútorňý Ø obrobku od	20 mm
Výška	293 mm
Druh produktu	Indukčný ohrievač