



Akumulátorový LED reflektor, Príkon: 13



ÚDAJE O OBJEDNÁVKE

Číslo objednávky	081285 13
GTIN	5708997362013
Trieda položky	08C

Popis

Prevedenie:

Sturdy LED floodlight with shock-resistant aluminium casing and rubber protective edge.

- **Soft non-shadowing anti-glare lamp, with low heat emission.**
- **High light output, low energy consumption.**
- **Certified for exterior use and for use in humid environments.**

NOVA "For Life" cordless floodlight with integrated carrying handle and 5-step dimmer function.

- **New, updated design with highly efficient multi-LEDs.**
- **New OPTILight function for optimised light output and superior duration.**
- **Compact and durable for demanding work environments.**

Funkcia:

IP67: Skladá sa z ochrany proti dočasnému ponoreniu do vody a z ochrany proti vniknutiu prachu (prachotesné), ako aj úplnej ochrany proti dotyku.

Rozsah balenia:

Vrátane nabíjacieho kábla USB a sieťovej časti so zástrčkou.

Technický opis

Zásobovanie energiou	Prevádzka s akumulátorom
----------------------	--------------------------

Technický list

Celková délka	163 mm
Celková výška	163 mm
Svetelný tok	200 - 2000 lm
Príkon	13 W
Celková šírka	63 mm
Druh batérie	Li-Ion
Stupeň ochrany krytom IP	IP 67