### Bit-Checks / Bit-Safes BiTorsion



















**EAN:** 4013288128157 **Size:** 200x95x16 mm

Part number:05073418001Weight:129 gArticle number:Bit-Check 10 BiTorsion 3 SB Country of origin:CZ

Customs tariff 82079030 number:

- Upright positionable, multi-component Bit-Check
- Rapidaptor holder for rapid bit change
- BiTorsion bits for long service life
- Tough viscous bits for universal use
- "Take it easy" tool finder: colour coding according to profile and size

Robust Bit-Checks by Wera. Bit-Checks provide a quick overview of the tools available. Bits not needed are simply reinserted into the set and do not get lost. Simple transportation e.g. in the shirt pocket. Extra-hard bits. BiTorsion bits with an Torsion zone - where kinetic energy is diverted from peak loads. This greatly extends the product service life. It provides the best possible durability together with the matching holder. Comes with Rapidaptor technology, which allows bits to be attached without any need to actuate the sleeve. The removal of the bit is simple, just by pushing the sleeve forward - for rapid bit change with just one hand. For the take-up of bits with ¼" hexagon head drive as per DIN ISO 1173-C 6.3 and E 6.3. For insertion in the power screwdriver or for use in the chuck of an electric drill.

### Bit-Checks / Bit-Safes BiTorsion



## At the workplace

### **BiTorsion Bits**

### **BiTorsion Rapidaptor**

### Above-average service life




The Bit-Checks can be positioned upright at the workplace so the tool is always quickly to hand.



With BiTorsion zone to cushion peak loads.



BiTorsion holders from Wera have a torsion spring design that absorbs smaller peak loads during screwdriving. The combined use with BiTorsion bits with their torsion zone distinctly extends the service life of the tool. Conveniently, BiTorsion holders from Wera can also be used with conventional bits.




Even the service life of conventional bits is enhanced with the use of the BiTorsion holder and the BiTorsion bit also functions in a normal holder.

### BiTorsion phase 1



The torsion spring integrated into the unique BiTorsion holder absorbs lower levels of peak loads (Phase 1). Any overloading of this spring is effectively prevented by means of a supporting mechanism.

# BiTorsion phase 2



Higher peak loads are minimised through the torsion effect of the bit shaft (Phase 2).

# BiTorsion and conventional tools



The BiTorsion holder and the BiTorsion bit can, of course, be used independently of one another.

# Rapid-in and self-lock



The bit can be pushed into the adaptor without moving the sleeve. The lock is activated automatically as soon as the bit is applied to the screw. Bits are held securely and wobble-free.

# Bit-Check 10 BiTorsion 3 SB, 10 pieces

### Bit-Checks / Bit-Safes BiTorsion




### Set contents:

# 897/4 R Rapidaptor BiTorsion Universal Bit Holder, 1/4" x 75 mm

05053923001 1x 1/4" x 75 mm



### 851/1 BTZ bits, PH 2 x 25 mm





### 855/1 BTZ bits, PZ 1 x 25 mm

<b>(</b>	05056720001	1x	PZ 1 x 25 mm
	05056722001	1x	PZ 2 x 25 mm
M Wera	05056724001	1x	PZ 3 x 25 mm

### 867/1 BTZ TORX® bits. TX 10 x 25 mm

CONTRACTOR DICE, TATTO A ECHIMIC				
	05066120001	1x	TX 10 x 25 mm	
Wera Wera	05066122001	1x	TX 15 x 25 mm	
	05066124001	1x	TX 20 x 25 mm	
	05066126001	1x	TX 25 x 25 mm	
	05066128001	1x	TX 30 x 25 mm	